... because a great day starts with a great night's sleep.





S6 Cold foam mattress

- An adaptable cold foam core made of high-quality HR cold foam with distinct body comfort zones for high reclining comfort
- Pressure relief for the spine using an intricate cutting technique with a cylinder structure for restful sleep
- Temperature and moisture balancing
- Low-maintenance thanks to removal, washable, or dry-clean safe covers
- Made in Germany

S6



Thanks to its special surface cutting with lengthwise and crosswise profiles, the S6 core made of HR cold foam is extremely adaptable and comfortable. Integral body zones offer soft yet firm support.



Selecta covers have a soft surface and are especially sturdy. They ensure excellent moisture balance.

Washable cover

All-around finish S860 Finished border S861

- Sturdy double jersey, 59% polyester, 41% viscose
- Quilted with approx. 400 g/m² of breathable fiber
- All-around zipper
- Separately removable cover
- Washable up to 60 °C

Wool ticking

All-around finish S160 Finished border S161

- Sturdy double jersey, 59% polyester, 41% viscose
- Quilted with approx. 500 g/m² of sheep's wool and approx. 200 g/m² of breathable fiber
- All-around zipper
- Separately removable cover
- Dry-clean safe



Core

- Highly elastic core made of high-quality HR cold foam with a density of 55 kg/m³
- Division into 7 anatomically designed functional zones
- Distinct comfort zones for shoulders with form-fitting cylinder cutting as well as integrated lumbar support and heel zone
- Longitudinal and transverse ventilation channels for excellent ventilation
- Core height approx. 16 cm Height with cover approx. 19 cm
- Firmness: soft, medium, firm

Recommended firmness

	Height cm				
	below 160	160-170	170-180	180-190	above 190
Weight kg					
below 50	soft	soft	soft	soft	soft
50-60	soft	soft	soft	soft	soft
60-70	medium	medium	medium	soft	soft
70-80	firm	medium	medium	medium	medium
80-90	firm	firm	firm	medium	medium
above 90	firm	firm	firm	firm	firm

Ergonomic cylindrical cuts in the shoulder area (the cylinders vary in diameter) allow your shoulders to sink in softly and deeply.



